

[See all 30 Products in Family](#)

**TECHSPEC® 30mm 50R/50T Cube Beamsplitter**



Stock #32-701 **14 In Stock**

⊖ 1 ⊕ **S\$442<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$442.40</b> each
Qty 6-25	<b>S\$354.20</b> each
Qty 26-99	<b>S\$324.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Standard Beamsplitter **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

Cube **Construction:**

30.0 x 30.0 x 30.0 ±0.10  
Dimensions (mm):

## Optical Properties

±3  
Beam Deviation (arcmin):

M4 MgF<sub>2</sub> @ 550nm on Faces  
Multilayer Dielectric on Hypotenuse  
Coating:

50/50  
Reflection/Transmission Ratio (R/T):

±5  
Reflection/Transmission Tolerance (%):

N-BK7  
Substrate: □

60-40  
Surface Quality:

400 - 700  
Wavelength Range (nm):

1.25  
Power (fringes) @ 632.8nm:

0.25  
Irregularity (fringes) @ 632.8nm:

## Regulatory Compliance

Compliant  
RoHS 2015:

Compliant  
Reach 223:

View  
Certificate of Conformance:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


Output is partially polarized. If polarization sensitivity is critical to your application, we recommend using [TECHSPEC® Polarizing Beamsplitters](#) or [TECHSPEC® Non-Polarizing Beamsplitters](#).

- Multi-Layer Dielectric Coating
- Available in 30/70, 70/30, or 50/50 Split Ratios
- Optimal for Applications Insensitive to Polarization

TECHSPEC® Cube Beamsplitters are constructed by cementing two right angle prisms together and are offered in a range of reflection/transmission ratios. Output is partially polarized, making this product suitable for illumination and other applications where polarization is not a concern. TECHSPEC® Cube Beamsplitters feature an interference coating which is applied to the hypotenuse surface of one of the prisms to provide the designated reflection/transmission ratio with minimal absorption loss.

**Note:** If polarization sensitivity is critical to your application, we recommend using [TECHSPEC® Polarizing Beamsplitters](#) or [TECHSPEC® Non-Polarizing Beamsplitters](#).

## Technical Information





---

;