

[See all 72 Products in Family](#)

**TECHSPEC® 30mm Dia. Linear Polarizing Film (XP42-40)**



Stock #71-357 **20+ In Stock**

S\$31<sup>.15</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	S\$31.15 each
Qty 11-25	S\$24.92 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

Polarization axis is parallel to notch on polarizer edge **Note:**

**Physical & Mechanical Properties**

30.00 +0.0/-0.3 **Diameter (mm):**

0.40 ±0.05 **Thickness (mm):**

Polarizing Film on PMMA

**Construction:**

**Optical Properties**

Uncoated, protective film on both sides

**Coating:**

9000:1 (nominal at 555nm)

**Extinction Ratio:**

**Substrate:**

**Polymer Film XP42-40**

**Transmission (%):**

Single: 42 ±2  
Parallel: 36.4  
Crossed: <0.004 (nominal at 555nm)

400 - 700

**Wavelength Range (nm):**

>99.98 (nominal at 555nm)

**Polarization Efficiency (%):**

42 ±2

**Transmission, Single (%):**

36.4

**Transmission, Parallel (%):**

<0.004 (nominal at 555nm)

**Transmission, Crossed (%):**

**Environmental & Durability Factors**

-10 to +60

**Operating Temperature (°C):**

**Regulatory Compliance**

[View](#)

**Certificate of Conformance:**

## Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information



XP44 - Linear Polarizer

