

TECHSPEC® 30mm Dia Enhanced Aluminum, $\lambda/20$ Mirror



Stock #34-362 **5 In Stock**

⊖ 1 ⊕ S\$305^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$305.20 each
Qty 6-25	S\$245.00 each
Qty 26-49	S\$229.60 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror Type:

Physical & Mechanical Properties

30.00 +0.0/-0.20 Diameter (mm):

5.00 ±0.20 Thickness (mm):

Commercial Polish **Back Surface:**

90.00 **Clear Aperture (%):**

Ground, protective bevel as needed **Edges:**

30.00 **Parallelism (arcsec):**

Optical Properties

Metal **Coating Type:**

Enhanced Aluminum (450-650nm) **Coating:**

$\lambda/20$ (flatness pre-coating) **Surface Flatness (P-V):**

450 - 650 **Wavelength Range (nm):**

Fused Silica (Corning 7980) **Substrate:**

$R_{avg} > 95\%$ @ 450 - 650nm **Coating Specification:**

20-10 **Surface Quality:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Precision Fused Silica Substrate
- 20-10 Surface Quality
- Low Coefficient of Thermal Expansion

TECHSPEC® $\lambda/20$ First Surface Mirrors are polished to industry leading surface accuracy and quality specifications to minimize reflected wavefront error. These mirrors feature a precision fused silica substrate with a low coefficient of thermal expansion. Multiple coating options are available, allowing these mirrors to be integrated into applications spanning the visible through infrared spectra. TECHSPEC® $\lambda/20$ First Surface Mirrors are ideal for beam steering and reflection applications and are available in a variety of size, thickness, and coating options.

Note: Surface flatness is measured before coating.

Technical Information



Range (nm)	% Reflection	Range (nm)	% Reflection	Range (nm)	% Reflection	Range (nm)	% Reflection	Range (nm)	% Reflection
0.4 - 0.7	85	0.45 - 0.65	95	0.25 - 0.45	89	0.7 - 2.0	96	0.45 - 2.0	98
0.4 - 2.0	90	-	-	0.25 - 0.70	85	2.0 - 10.0	96	2.0 - 10.0	98

Coating Curves

Compatible Mounts
