

## TECHSPEC® 30mm Dia. High Performance Glass Linear Polarizer



Stock #49-078 3-5 DAYS

⊖ 1 ⊕ **S\$291.45**

**ADD TO CART**

Qty 1-5

**S\$291.45**

Qty 6+

**S\$233.45**

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Coating:**  
AR: R<sub>avg</sub> <0.5% @ 400 - 700nm

**Diameter (mm):**  
30.00

**Extinction Ratio:**  
10,000:1

**Substrate:**   
Polymer Film between [B270](#)

**Operating Temperature (°C):**  
-25 to +65

**Thickness (mm):**  
2.00

**Thickness Tolerance (mm):**  
±0.2

**Transmission (%):**  
25 (for random polarization)

**Transmission Tolerance (%):**  
±2

**Type:**  
Linear Polarizer

**Parallelism (arcmin):**  
<4

**Dimensional Tolerance (mm):**  
+0.0/-0.2

**Construction:**  
Dichroic Polarizing Film between Glass

**Wavelength Range (nm):**  
400 - 700

**Surface Flatness (P-V):**  
<1λ

**Polarization Axis Mark (°):**  
±2

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 224:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---