

[See all 17 Products in Family](#)

**TECHSPEC® 30mm Dia. Linear Polarizer Film (XP42HE-40)**



Stock #71-894 **20+ In Stock**

- 1 + **\$54.<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>\$54.60</b> each
Qty 11-25	<b>\$43.68</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

**Note:**  
Polarization axis can be identified as follows:  
Circular Parts - Parallel to direction of notch on polarizer  
Square Parts - Parallel to mark on protective film  
Rectangular Parts - Parallel to first listed dimension

**Physical & Mechanical Properties**

**Diameter (mm):**

30.00 +0/-0.3

**Thickness (mm):**

0.40 +/- 0.05

**Construction:**

Polarizing Film

## Optical Properties

**Extinction Ratio:**

30,000:1 (Nominal at 555nm)

**Substrate:** □

Polymer Film XP42HE-40

**Transmission (%):**

Single: 42.6 (nominal @ 555nm), 41.1 (average 420-700nm)  
Parallel: 36.4 (nominal @ 555nm), 34.0 (average 420-700nm)  
Crossed: 0.001 (nominal @ 555nm), 0.002 (average 420-700nm)

**Wavelength Range (nm):**

420 - 700

**Polarization Efficiency (%):**

>99.99% (nominal at 555nm)

## Environmental & Durability Factors

**Operating Temperature (°C):**

-10 to +60

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**REACH 241:**

[Compliant](#)

## Product Details

- Superior 30,000:1 Extinction Ratio
- Excellent Transmission from 420-700nm
- Available in a Range of Sizes
- Custom Sizes Available

TECHSPEC® Ultra-High Contrast Polarizing Film (XP42HE) are designed to produce a 30,000:1 contrast ratio from 420 – 700nm with an excellent transmission of 42.6%. These polarizing films are available in rectangular geometries in a range of sizes. TECHSPEC Ultra-High Contrast Polarizing Film (XP42HE) are easily cut to required geometries using common cutting tools for system integration. Additionally, the 500 x 1000mm version [#24-286](#) and [#71-907](#) are available with an adhesive backing to facilitate incorporation into various applications. These polarizing films are ideal for imaging, metrology, and microscopy applications where contrast sensitivity is paramount.