

[See all 17 Products in Family](#)

# 30x60mm Half Mirror Coaxial Light Red

See More by [CCS](#)



Stock #21-832 **CLEARANCE** 1 In Stock

⊖ 1 ⊕ **\$3,486.00**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$3,486.00</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

LFV3-G-30X60RD **Model Number:**

LED Illuminator **Type of Illumination:**

CCS **Manufacturer:**

Coaxial Light **Geometry:**

Constant **Illumination Mode:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
W 68 mm x D 60 mm x H 35 mm

**Weight (g):**  
165

**Active Area (mm):**  
30 mm x 60 mm

## Optical Properties

**Color:**  
Red

**Wavelength (nm):**  
630

## Electrical

**Power Consumption (W):**  
11

## Hardware & Interface Connectivity

**Input Voltage (V):**  
24

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#73-491](#)  
Europe: [#73-491](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#73-491](#)

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Reach 224:**  
[Contains SVHC\(s\)](#)

**Certificate of Conformance:**  
[View](#)


## Product Details

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

## Technical Information

### Imaging Example: Imaging Comparison of Resolution Evaluation Chart



[Imaging conditions] Camera: 2448x2048 3.45 µm monochrome camera, Lens: 2x telecentric lens, Field of view: 4.2 x 3.5 mm (the image is a cutout of about 1.3 x 1.0 mm at the center), Resolution: 1.7 µm/pixel, WD: 110 mm, LWD: 25 mm. \*The shutter speed and light intensity are adjusted for each image.