


TECHSPEC[®] 3.2mm Dia. x 4.0mm Length Telecom-NIR Coated, N-LASFN9 Drum Lens



Stock **#45-745** CLEARANCE **20+ In Stock**

-

1

+

S\$29^{.80}

ADD TO CART

Volume Pricing	
Qty 1+	S\$29.80 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Drum Lens

Physical & Mechanical Properties

Diameter (mm):
3.20

4.00	Length (mm):
±3	Length Tolerance (µm):
2.00	Radius R (mm):
+0/-1.5	Radius Tolerance (µm):
+0/-50	Diameter Tolerance (µm):

Optical Properties	
N-LASF9	Substrate: □
Telecom-NIR	Coating:
1295 - 1565	Wavelength Range (nm):
Coating Specification: R _{abs} ≤0.25% @ 1295 - 1325nm R _{abs} ≤0.25% @ 1535 - 1565nm	
1.850	Index of Refraction (n _d):
40-20	Surface Quality:

Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Easier to Mount and Handle Than Standard Ball Lenses
- Drum lenses are glass spheres, ground down axially to provide a mounting surface. The ground circumference D simplifies handling issues typically associated with ball lenses. Ideal for optical transmission in fiber communications. Type B Drum lenses have a polished plano-surface for direct fiber contact and perform as elongated PCX lenses.

TECHNICAL INFORMATION

D	Radius R	Length	Length L2	Stock No.
Type A Drum Lenses				
2mm	1.25mm	2.5mm	1.5mm	#45-548
				#45-739
				#45-836
				#45-663
				#45-743
2.4mm	1.5mm	3mm	1.8mm	#45-549
				#45-837
				#45-664
				#45-744
3.2mm	2mm	4mm	2.4mm	#45-550
				#45-741
				#45-838
				#45-665
				#45-745
4mm	2.5mm	5mm	3mm	#45-551
				#45-839
				#45-742
				#45-666
Type B Half-Drum Lenses				
2mm	1.25mm	2mm	1.5mm	#46-524
				#46-528
2.4mm	1.5mm	2.4mm	1.8mm	#46-525
				#46-529
3.2mm	2mm	3.2mm	2.4mm	#46-526
				#46-530

