

32mm Dia. x -200mm FL, Grade 2, Double-Concave Lens



Stock #53-113 CLEARANCE **20+ In Stock**

S\$15^{.75}

ADD TO CART

Volume Pricing

Qty 1+	S\$15.75 each
Need More?	Request Quote

Product Downloads

General

Double-Concave Lens **Type:**

Physical & Mechanical Properties

32.00 **Diameter (mm):**

Optical Properties

-200.00 **Effective Focal Length EFL (mm):**

f#:

6.25

Numerical Aperture NA:

0.08

Material Properties

Grade:

Grade 2

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-concave (DCV) lenses have two inward curved surfaces and a negative focal length. They are used for image reduction and to spread light.

Experimental Quality Double-Concave (DCV) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

