

30W Deuterium / 5W Tungsten Lamp



30W Deuterium / 5W Tungsten Lamp, #87-300

Stock **#87-300** 2 In Stock

-

1

+

S\$5,530⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$5,530.00 each
Need More?	Request Quote

Product Downloads

General	
Note: Built-in power supply. AC power cord included. Fiber patchcord listed under Accessories tab sold separately.	
≥2000 / ≥10,000	Lamp Lifetime (hours):
Physical & Mechanical Properties	
220 x 187 x 130	Dimensions (mm):

Optical Properties	
190 - 2500	Wavelength Range (nm):
Electrical	
30W Deuterium 5W Tungsten	Output Power (W):
Hardware & Interface Connectivity	
SMA-905	Connector:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.