

## 32.5mm Dia. x 23.5mm FL, Aspheric Condenser Lens



Stock #19-519 **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **\$76<sup>30</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-10	<b>\$76.30</b> each
Qty 11-49	<b>\$68.60</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

32.50 +0.0/-0.2 **Diameter (mm):**

≤30 **Centering (arcmin):**

**Clear Aperture CA (mm):**

29.25	Edge Thickness ET (mm):
1.85	
Center Thickness CT (mm):	
13.50 ±0.30	
Bevel:	
Protective as needed	
Diameter of Asphere (mm):	
32.5	
Shape of Back Surface:	
Convex	

### Optical Properties

Effective Focal Length EFL (mm):	
23.50	
Numerical Aperture NA:	
0.69	
Back Focal Length BFL (mm):	
15	
Substrate: <input type="checkbox"/>	
H-K51	
Focal Length Tolerance (%):	
±5	
Coating:	
Uncoated	
Surface Quality:	
80-50 (typical)	
f#:	
0.72	
Radius R <sub>2</sub> (mm):	
165	
Wavelength Range (nm):	
350 - 2000	
Conjugate Distance:	
Infinite	

### Regulatory Compliance

Certificate of Conformance:	
<a href="#">View</a>	

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information



