

[See all 157 Products in Family](#)

TECHSPEC<sup>®</sup> 35 x 35mm 30R/70T, NIR Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#49-753** 17 In Stock

-

1

+

S\$313<sup>60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$313.60 each                |
| Qty 6-25       | S\$245.00 each                |
| Qty 26-99      | S\$226.80 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Note:

Beamsplitter-coated side is marked with a black dot

Type:

Standard Beamsplitter

Physical & Mechanical Properties

Clear Aperture (%):

>85


|                                                                                                                              |                                      |
|------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|
| Plate                                                                                                                        | Construction:                        |
| 35.0 x 35.0 +0.0/-0.25                                                                                                       | Dimensions (mm):                     |
| Cut with 0.25mm maximum edge chip                                                                                            | Edges:                               |
| ≤3                                                                                                                           | Parallelism (arcmin):                |
| 3.00 ±0.25                                                                                                                   | Thickness (mm):                      |
| Optical Properties                                                                                                           |                                      |
| 45                                                                                                                           | Angle of Incidence (°):              |
| Surface 1: 30/70 ±5% @ 900nm, ±10% @ 700 - 1100nm<br>Surface 2: AR R <sub>avg</sub> ≤1%, R <sub>abs</sub> ≤2% @ 700 - 1100nm | Coating Specification:               |
| 30/70                                                                                                                        | Reflection/Transmission Ratio (R/T): |
| N-BK7                                                                                                                        | Substrate: □                         |
| 1λ per inch                                                                                                                  | Surface Flatness (P-V):              |
| 60-40                                                                                                                        | Surface Quality:                     |
| 700 - 1100                                                                                                                   | Wavelength Range (nm):               |
| Regulatory Compliance                                                                                                        |                                      |
| Compliant                                                                                                                    | RoHS 2015:                           |
| View                                                                                                                         | Certificate of Conformance:          |
| Compliant                                                                                                                    | Reach 247:                           |

Product Details

- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- [C-Mounted Plate Beamsplitters](#) Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification [imaging](#) systems and for combining low power [laser](#) beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.

Technical Information





## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

