

350 - 1100nm, UV Block C-Mount Protective Window



C-Mount Camera Imaging Filters

Stock **#73-313** **4 In Stock**

-

1

+

S\$147⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$147.00 each
Qty 10+	S\$139.30 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):

19.50

Outer Diameter (mm):

25.40

Construction:

Mounted in Black Anodized Ring	
1.00	Substrate Thickness (mm):
Optical Properties	
285.00	Cut-On Wavelength (nm):
≥98	Minimum Transmission (%):
AR Hard Coated	Coating:
UV	Color:
40-20	Surface Quality:
350 - 1100	Transmission Wavelength (nm):
Threading & Mounting	
C-Mount	Filter Thread:
3.00	Mount Thickness (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Threads Directly between a Lens and any C-Mount Camera
- Narrow UV, VIS and SWIR Bandpass Filters Available
- Recommended for Wide Angle Lenses
- UV Protective Windows Available

C-Mount Camera Imaging Filters feature narrow imaging bandpass filters, covering the UV, VIS, and SWIR spectral ranges and are designed with anti-reflection coatings to minimize light loss and enhance performance. These filters are designed to thread directly into any C-mount camera, between the lens and sensor, to ensure compatibility across devices and are particularly useful in applications with space constraints or lenses without filter threads. A custom installation wrench is included with each filter. C-Mount Camera Imaging Filters achieve high transmission rates, typically exceeding 85%, while maintaining a narrow bandwidth, allowing them to selectively transmit a specific wavelength range. These imaging filters are ideal for applications where precise wavelength selection is crucial for optimal imaging and detection such as; Food & Agricultural Inspection, Densitometry, Remote Sensing, and Security and Surveillance.

Note: UV Protective Windows offering low absorption and excellent thermal stability are available for imaging applications between 350 – 1100nm.