

35mm 2 MegaPixel Fixed Focal Length Lens



35mm Fixed Focal Length, #14-400

Stock **#14-400** **2 In Stock**

-

1

+

S\$465⁴⁵

ADD TO CART

Volume Pricing	
Qty 1+	S\$465.45 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Fixed Focal Length Lens

Type:

Physical & Mechanical Properties

Variable

Iris Option:

36.91	Length (mm):
32.5	Maximum Diameter (mm):
90	Weight (g):
Optical Properties	
14.4°	Horizontal Field of View @ Max Sensor Format:
14.4°	Horizontal Field of View, 2/3" Sensor:
10.5°	Horizontal Field of View, 1/2" Sensor:
8°	Horizontal Field of View, 1/3" Sensor:
5.23°	Horizontal Field of View, 1/4" Sensor:
11.00	Maximum Image Circle (mm):
35.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
f/1.4 - f/32	Aperture (f/#):
<-1	Distortion (%):
VS	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M30.5 x 0.50 (Female)	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover 1/2" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.