

[See all 39 Products in Family](#)

355nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-248** [CONTACT US](#)

☐ [Additional Bandwidths](#)

-

1

+

S\$1,192⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,192.80 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
≥22	Clear Aperture CA (mm):
±0.10	Thickness Tolerance (mm):

Mounted in Black Anodized Ring	Construction:
ML-C-48497A	Physical Durability: Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3
Substrate Thickness (mm):	
2.0 ±0.1	

Optical Properties	
0 ±2	Angle of Incidence (°):
1.3	Bandwidth (nm):
<11	Beam Deviation (arcsec):
OD 5 Blocking Wavelength Range (nm) : 315 - 352 & 359 - 423	
OD 6 Blocking Wavelength Range (nm): 327 - 350 & 360 - 390	
Optical Density OD (Average): ≥6.0	
Center Wavelength CWL (nm): 355.00	
Design Wavelength DWL (nm): 355	
Full Width-Half Max FWHM (nm): 1.35 - 2.49	
Substrate: Fused Silica	
Minimum Transmission (%): >90	
Coating: Hard Coated	
Surface Quality: 60-40	
Transmission (%): >90	
Blocking Wavelength Range (nm): 315 - 352 & 359 - 423	
Transmitted Wavefront, P-V: ¼ @ 633nm	

Threading & Mounting	
Mount Thickness (mm): 3.5 ±0.1	

Environmental & Durability Factors	
Temperature Dependence (ppm/°C): <5	
Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
Certificate of Conformance: View	







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts