

TECHSPEC® 35mm f/1.85, UCi Series Fixed Focal Length Lens



35mm UCi Series Fixed Focal Length Lens



Stock #33-897 13 In Stock

-

1

+

S\$329⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$329.00 each
Need More?	Request Quote

Product Downloads

General	
UCi Series	Product Family:
Fixed Focal Length Lens	Type:
No	IR Cut Filter:
High Performance Lens with Compact Form Factor	Imaging Lens Type:

and Fixed Aperture

Physical & Mechanical Properties

Fixed	Iris Option:
52.19	Length (mm):
26.5	Maximum Diameter (mm):
26.5	Outer Diameter (mm):
2.21	Maximum Rear Protrusion (mm):
52.19	Maximum Length (mm):

Optical Properties

45.6mm - 11.9°	Horizontal Field of View @ Max Sensor Format:
Horizontal: 45.6mm - 11.9° Vertical: 34.1mm - 8.9° Diagonal: 57.2mm - 14.9°	Field of View at Max Sensor Format:
45.6mm - 11.9°	Horizontal Field of View, 1/1.8" Sensor:
40.5mm - 10.6°	Horizontal Field of View, 1/2" Sensor:
36.7mm - 9.6°	Horizontal Field of View, 1/2.5" Sensor:
30.3mm - 7.9°	Horizontal Field of View, 1/3" Sensor:
22.7mm - 6.0°	Horizontal Field of View, 1/4" Sensor:
9.00	Maximum Image Circle (mm):
0.0394	Numerical Aperture NA, Object Side:
7 (5)	Number of Elements (Groups):
35.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/1.85	Aperture (f/#):
N4 MgF ₂	Coating:
N4 MgF ₂	Coating Specification:
34.01	Entrance Pupil Position (mm):
49.25	Object Space Principal Plane (mm):
-19.45	Image Space Principal Plane (mm):
-0.22	Maximum Distortion (%):
-46.71	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1/2.5"	Optimized Sensor Format:
1/1.8"	Maximum Sensor Format:
1.85	Pixel Size (µm):

Threading & Mounting

N/A	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

-20 to +60	Storage Temperature (°C):
	Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)	

Regulatory Compliance

View	Certificate of Conformance:
---------------------------------------	--

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels ≤2.2µm and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


Technical Information




#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Distortion Plot




#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f1.8



#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Depth of Field Plot, 400mm Working Distance, f1.8



#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f1.8



#33-897, 35mm f/1.85, UCi Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f1.8

Compatible Cameras