

TECHSPEC®

35mm, f/8 Sealed UCw Series Fixed Focal Length Lens



UCw Series Fixed Focal Length Lenses

Stock **#70-628** NEW **2 In Stock**

-

1

+

S\$335⁶⁵

ADD TO CART

Volume Pricing	
Qty 1+	S\$335.65 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Ucw Series	Series:
Fixed Focal Length Lens	Type:

High Performance Lens with Compact Form Factor	Imaging Lens Type:
--	--------------------

Physical & Mechanical Properties	
Fixed	Iris Option:
51.46	Length (mm):
38	Maximum Diameter (mm):
38	Outer Diameter (mm):
2.11	Maximum Rear Protrusion (mm):
52.76	Maximum Length (mm):
Optical Properties	
11.1°	Horizontal Field of View @ Max Sensor Format:
11.9°	Horizontal Field of View, 1/1.8" Sensor:
10.6°	Horizontal Field of View, 1/2" Sensor:
9.6°	Horizontal Field of View, 1/2.5" Sensor:
7.9°	Horizontal Field of View, 1/3" Sensor:
6.0°	Horizontal Field of View, 1/4" Sensor:
9.00	Maximum Image Circle (mm):
0.01	Numerical Aperture NA, Object Side:
7 (5)	Number of Elements (Groups):
35.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/8.0	Aperture (f/#):
N4 MgF ₂	Coating:
N4 MgF ₂	Coating Specification:
34.01	Entrance Pupil Position (mm):
49.24	Object Space Principal Plane (mm):
-19.45	Image Space Principal Plane (mm):
-0.22	Maximum Distortion (%):
-46.71	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
Sensor	
1/2.5"	Optimized Sensor Format:
1/1.8"	Maximum Sensor Format:
Threading & Mounting	
M25.5 x 0.50 (Female)	Filter Thread:
C-Mount	Mount:
Environmental & Durability Factors	
IPX7	Environmental Rating:
-20 to +60	Storage Temperature (°C):
	For questions regarding operating temperature please contact our support team

Type of Ruggedization:	
Waterproof (IPX7)	

Regulatory Compliance

Certificate of Conformance:	
View	

PRODUCT DETAILS

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.