


Siemens Star Target Array, 101 x 101mm, 59 Stars, 36 Sectors Chrome on Glass



Stock **#58-835** 1 In Stock

-

1

+

S\$1,260^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$1,260.00 each
Qty 5+	S\$1,197.56 each
Need More?	Request Quote

Product Downloads

General

No	NIST Certification:
----	---------------------

Physical & Mechanical Properties

4.50	Individual Star Diameter (mm):
36.00	Number of Sectors:

59.00	Number of Stars:
-------	------------------

90.00 x 90.00	Pattern Size (mm):
101 x 101 ±0.1	Dimensions (mm):
2.00 ±0.05	Thickness (mm):
Optical Properties	
High Reflective Chrome	Coating:
1.27 - 38.5	Frequency (lp/mm):
Float Glass	Substrate:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 223:
View	Certificate of Conformance:

Product Details

- Detect Aberrations at Various Field Points
Our star target arrays are designed to identify focus errors and astigmatism along field points in the image of a vision system. With star targets located at the center, corner, and along the diagonals of the sensor, determining precision location and amplitude of the problem areas couldn't be easier. The small array features unresolved centers of 0.1mm, whereas the large array features unresolved centers of 0.15mm.