



[See all 3 Products in Family](#)

# 38.1mm Dia., 3mm Thick, Uncoated, ISP Optics Lithium Fluoride (LiF) Window | LF-W-38-3

See More by [ISP Optics](#)



Stock ~~#24-477~~ **CLEARANCE** 2 In Stock

⊖ 1 ⊕ **\$\$362<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	\$362.60 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

LF-W-38-3 **Model Number:**

Protective Window **Type:**

Crystal **Type of Window:**

### Physical & Mechanical Properties

32.38	Clear Aperture CA (mm):
38.10 +0.00/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.33	Poisson's Ratio:
64.97	Young's Modulus (GPa):
102.00	Knoop Hardness (kg/mm <sup>2</sup> ):

## Optical Properties

Uncoated	Coating:
Lithium Fluoride (LiF)	Substrate: <input type="checkbox"/>
1.392	Index of Refraction (n <sub>d</sub> ):
60-40	Surface Quality:
97.29	Abbe Number (v <sub>d</sub> ):
Random	Axis Orientation:
150 - 6000	Wavelength Range (nm):
2λ @ 632.8nm	Surface Flatness (P-V):

## Material Properties

2.64	Density (g/cm <sup>3</sup> ):
37	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
----------------------	-----------------------------

## Product Details

- Excellent Vacuum UV (VUV) Transmission
- High Transmission from 150nm - 6µm
- Low Index of Refraction

ISP Optics Lithium Fluoride (LiF) Windows provide excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 – 200nm, as well as at the hydrogen Lyman-alpha line (121nm). In addition to high transmission into the UV, these windows also feature superior transmission in the Visible and Infrared up to 6µm. Lithium fluoride has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. ISP Optics Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

**Note:** Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

