


**TECHSPEC® 38.1 x 25.4mm 1064nm 45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-656** **6 In Stock**

⊖ 1 ⊕ **\$259<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | <b>\$259.00</b> each          |
| Qty 6-25       | <b>\$229.60</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

85 **Clear Aperture (%):**

**Back Surface:**

Commercial Polish

38.1 x 25.4 +0.00/-0.10

Dimensions (mm):

6.35 ±0.20

Thickness (mm):

## Optical Properties

10-5 **Surface Quality:**

99.8 **Reflection at DWL (%):**

**Coating Specification:**  
R<sub>abs</sub> >99.8% @ 1064nm  
R<sub>avg</sub> >99.5% @ 1046 - 1074nm

1046 - 1074 **Wavelength Range (nm):**

λ10 **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (1046-1074nm) **Coating:**

1064 **Design Wavelength DWL (nm):**

45 **Angle of Incidence (°):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Damage Threshold, Reference:**   
20 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **REACH 201:**

[View](#) **Certificate of Conformance:**

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts