

[See all 8 Products in Family](#)

38.1mm Dia. x 250mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) PCX Lens | CF-PX-38-250

See More by [ISP Optics](#)



Stock #24-810 CLEARANCE **3 In Stock**

S\$424²⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$424.20 each
Need More?	Request Quote

Product Downloads

General

Type:
 Plano-Convex Lens

Model Number:
 CF-PX-38-250

Physical & Mechanical Properties

Diameter (mm):
 38.10 +0.00/-0.13

<3	Centering (arcmin):
3.80 ±0.20	Center Thickness CT (mm):
3.80	Edge Thickness ET (mm):
34.29	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

250.00 @5µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: <input type="checkbox"/>
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
±2	Focal Length Tolerance (%):
100.00	Radius R₁ (mm):
6.56	f#:
0.08	Numerical Aperture NA:
300 - 8000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Greater than 90% Transmission from 0.35-7µm
- Low Index of Refraction
- Ideal for Integration into Infrared Systems

ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses provide greater than 90% transmission from 350nm to 7µm and feature a low refractive index, allowing them to be used without an Anti-Reflection (AR) coating. Calcium Fluoride features a high laser damage threshold and low stress birefringence, making them highly suitable for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses are ideal for demanding applications that require superior performance from the visible through the mid-wave infrared (MMR) spectra.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools