

[See all 413 Products in Family](#)

TECHSPEC<sup>®</sup> 25.4mm Dia. x 75.0mm FL, VIS-EXT Coated, Plano-Convex Lens



Stock **#38-474** **5 In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$75<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | <b>S\$75.60</b> each          |
| Qty 10-24      | <b>S\$67.90</b> each          |
| Qty 25-49      | <b>S\$60.55</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.0/-0.025

|                      |                           |
|----------------------|---------------------------|
| <1                   | Centering (arcmin):       |
| 3.50 ±0.10           | Center Thickness CT (mm): |
| 1.36                 | Edge Thickness ET (mm):   |
| 24.4                 | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                                      |                                                       |
|--------------------------------------|-------------------------------------------------------|
| Optical Properties                   |                                                       |
| 75.00 @ 587.6nm                      | Effective Focal Length EFL (mm):                      |
| 72.69                                | Back Focal Length BFL (mm):                           |
| VIS-EXT (350-700nm)                  | Coating:                                              |
| R <sub>avg</sub> <0.5% @ 350 - 700nm | Coating Specification:                                |
| N-BK7                                | Substrate: <input type="checkbox"/>                   |
| 40-20                                | Surface Quality:                                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                                |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:                         |
| ±1                                   | Focal Length Tolerance (%):                           |
| 38.76                                | Radius R <sub>1</sub> (mm):                           |
| 2.95                                 | f/#:                                                  |
| 0.17                                 | Numerical Aperture NA:                                |
| 350 - 700                            | Wavelength Range (nm):                                |
| 5 J/cm² @ 532nm, 10ns                | Damage Threshold, By Design: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |


## Product Details

- Visible Broadband Anti-Reflection Coating with Extended UV Performance
- AR Coated to Provide <0.5% Reflectance per Surface for 350 - 700nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [YAG-BBAR](#)

TECHSPEC® VIS-EXT Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® VIS-EXT Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [YAG-BBAR](#).

## Technical Information



|                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N-BK7                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <div data-bbox="262 148 1249 667"><h3>Uncoated N-BK7 Typical Transmission</h3></div>                       | <div data-bbox="1339 356 1843 445"><p>Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                                                                                                                                                                                                                                                              |
| <div data-bbox="262 742 1207 1216"><h3>N-BK7 with MgF<sub>2</sub> Coating Typical Transmission</h3></div> | <div data-bbox="1339 831 1843 1083"><p>Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                             |
| <div data-bbox="262 1261 1239 1855"><h3>N-BK7 with VIS-EXT Coating Typical Transmission</h3></div>       | <div data-bbox="1339 1424 1843 1676"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.5\% @ 350 - 700\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                  |
| <div data-bbox="262 1899 1228 2463"><h3>N-BK7 with VIS-NIR Coating Typical Transmission</h3></div>       | <div data-bbox="1339 2018 1843 2329"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 0.25\% @ 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |
| <div data-bbox="262 2507 1165 2878"><h3>N-BK7 with VIS 0° Coating Typical Transmission</h3></div>        | <div data-bbox="1339 2656 1843 2893"><p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                   |

[CLICK HERE TO DOWNLOAD DATA](#)

Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 532nm$   
 $R_{abs} \leq 0.25\% @ 1064nm$   
 $R_{avg} \leq 1.0\% @ 500 - 1100nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR I  
(600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.5\% @ 750 - 800nm$   
 $R_{abs} \leq 1.0\% @ 800 - 1550nm$   
 $R_{avg} \leq 0.7\% @ 750 - 1550nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts