

Optotune 3mm Clear Aperture, VIS Coated, Electrically Focus Tunable Lens | EL-3-10-VIS-26D-FPC

See More by [Optotune](#)



Stock **#37-344** 12 In Stock

-

1

+

S\$245⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$245.00 each
Need More?	Request Quote

Product Downloads

General	
Specialty Lens	Type:
>1,000,000,000	Lifecycles:
EL-3-10-VIS-26D-FPC	Model Number:
<5 (80% step response)	Settling Time (ms):

Physical & Mechanical Properties	
3	Clear Aperture CA (mm):
10.0	Outer Diameter (mm):
4.00	Thickness (mm):
Optical Properties	
Low Dispersion Polymer	Substrate: ☐
BBAR (420-900nm)	Coating:
420 - 900	Wavelength Range (nm):
100	Abbe Number (v _d):
-13 to +13 diopter -77 to +77mm	Focus Range (mm):
1.300	Index of Refraction (n _d):
0.2λ @ 525nm	Transmitted Wavefront Error, RMS:
3W/cm ² @ 1064nm	Damage Threshold, By Design: ☐
Electrical	
-120 to +120	Current (mA):
0 - 0.12	Power Consumption (W):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Continuous Focusability
- Compact Size
- Wide Focal Adjustment Range

Optotune Focus Tunable Lenses 3mm Clear Aperture FPC Connector are easily integrated into a variety of Machine Vision applications including inspection, sorting, and bar code reading. By applying a current, the Optotune Focus Tunable Lenses 3mm Clear Aperture FPC Connector are able to quickly change shape from concave to convex, and provides an adjustment of -13 to +13 diopters (-77 to +77mm). With a small form factor of 10mm diameter x 4mm thick, low power consumption, and fast settling time, these lenses are the ideal option for OEM integration.