

TECHSPEC[®] 3X, UV Draconis[®] Broadband Beam Expander



TECHSPEC[®] Draconis[™] Broadband Beam Expanders

Stock **#68-270** 1 In Stock

-

1

+

S\$1,153⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$1,153.00 each
Qty 5-24	S\$1,015.00 each
Qty 25-99	S\$905.00 each
Need More?	Request Quote

Product Downloads

General	
Beam Expander	Type:
Fixed Magnification	Style:
Physical & Mechanical Properties	
88.00	Length (mm):


133	Weight (g):
46	Housing Diameter (mm):
Optical Properties	
11	Entrance Aperture (mm):
33	Exit Aperture (mm):
3X	Expansion Power:
Fused Silica (Corning 7980)	Substrate: ☐
0	Angle of Incidence (°):
Laser V-Coat (266nm, 355nm)	Coating:
Broadband	Design Wavelength DWL (nm):
M/10 @ 1mm Input Beam, M/4 @ 4mm Input Beam	Transmitted Wavefront, P-V:
260 - 365	Wavelength Range (nm):
R _{abs} <0.25% @ 265 - 267nm R _{abs} <0.25% @ 354 - 356nm R _{avg} <1% @ 260 - 365nm	Coating Specification:
Non-Rotating Optics	Divergence Adjustment:
Threading & Mounting	
Input: Male C-Thread (1" x 32 TPI) Output: Male T2-Thread (M42 x 0.75)	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- AR Coated for Broadband Tunable Laser Sources
 - Fixed Magnifications Available from 3X to 10X
 - Divergence Adjustable through Non-Rotating Optical Design for Reduced Beam Wander
- TECHSPEC® Draconis® Broadband Beam Expanders feature high performance optical designs that have been optimized and tested for broadband use. These beam expanders eliminate the need for critical alignment due to their diffraction-limited performance over large input beam diameters and wide acceptance angles. Their broadband designs enable use with multiple laser lines or tunable lasers, reducing the number of beam expanders required in optical systems. Additionally, the optical design ensures internal focusing of ghost images is not present, which allows compatibility with high power lasers. Mechanical adjustment through a sliding optical design corrects errors in divergence or collimation. TECHSPEC Draconis Broadband Beam Expanders' C and T input/output mounting threads are compatible with Edmund Optics' line of threaded mounting components, or mounting can be achieved using an optional mounting clamp.
- TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders are also available. For more cost sensitive applications, Edmund Optics also offers TECHSPEC Scorpii® Nd:YAG Beam Expanders. For HeNe laser applications, TECHSPEC Arcturus® HeNe Beam Expanders are available. For applications where rotating optics are acceptable, the TECHSPEC Vega® Laser Line Beam Expanders and TECHSPEC Vega® Broadband Beam Expanders are available. For broadband or ultrafast applications, TECHSPEC Canopus® Reflective Beam Expanders are available.



Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).