

TECHSPEC® 400 - 750nm, 25.2 x 35.6mm, Dichroic Longpass Filter Kit (8 Filters)



Stock #15-104

CONTACT US

-

1

+

S\$1,925^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,925.00 each
Need More?	Request Quote

Product Downloads

General

Filters Included :
Cut-on Wavelengths: [400nm](#), [450nm](#), [500nm](#),
[550nm](#), [600nm](#), [650nm](#), [700nm](#), [750nm](#)

Type:
Longpass Filter

Number of Filters:
8

Physical & Mechanical Properties

Dimensions (mm):
25.2 x 35.6

35.60	Length (mm):
25.20	Width (mm):
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497ASection 4.5.4.2	

Environmental & Durability Factors	
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7	

Regulatory Compliance	
Certificate of Conformance: View	

Product Details


- Ideal for Fluorescence or Multispectral Imaging
- Sharp Cut-On Wavelength
- Broad Transmission and Reflection Ranges

Our TECHSPEC® Dichroic Longpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral [beamsplitters](#). These hard coated filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. Reflection and transmission curves are available to easily integrate TECHSPEC® Dichroic Longpass Filters into any application.

Note: The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

Hard coatings are used to increase durability while maintaining performance. The hard coating provides Dichroic Longpass Filters with high resistance to humidity, temperature, and abrasion, while also reducing the risk of damage when being handled.

Technical Information



Filter Type	Transmitted Wavefront (RMS)	Surface Quality	Surface Flatness (P-V)	R(avg)	T(avg)
HP Dichroic	$\lambda/10$	40-20	$\lambda/2$	>98%	>90%
Fluorescence Dichroics	1 λ	60-40	-	>98%	>90%
Dichroic Longpass	$\lambda/4$	40-20	-	>97%	>85%