


400μm 0.22 NA UV/VIS Fiber, 25m Length



Stock **#57-075** [CONTACT US](#)

-

1

+

S\$784⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$784.00 each
Qty 5-24	S\$694.40 each
Need More?	Request Quote

Product Downloads

General	
Note: Fiber ends are not polished.	
Physical & Mechanical Properties	
Cladding Diameter (μm): 440 ±8.8	
Minimum Bend Radius (mm): 88/44 (Continuous/Momentary)	

25.00	Length (m):
480 ±10	Outer Diameter (µm):
400 ±8	Core Diameter (µm):
Optical Properties	
25.4	Acceptance Angle (°):
UV/MS	Coating:
Fused Silica	Substrate: □
0.22	Numerical Aperture NA:
1.457	Index of Refraction (n _d) - Core:
1.439	Index of Refraction (n _d) - Cladding:
190 - 1250	Wavelength Range (nm):
±0.02	Numerical Aperture (NA) Tolerance:
Material Properties	
Polyimide	Buffer Material:
Environmental & Durability Factors	
-190 to +390	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50µm – 600µm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600µm.

Note: Fiber ends are not polished.

Technical Information

