

400nm CWL, 11.8mm Dia. Bandpass Filter



Stock **#28-404** CLEARANCE **15 In Stock**

-

1

+

S\$27^{.93}

ADD TO CART

Volume Pricing	
Qty 1+	S\$27.93 each
Need More?	Request Quote

Product Downloads

General

Type:	
Bandpass Filter	
Typical Applications:	
Clinical Chemistry	

Physical & Mechanical Properties

Diameter (mm):	
11.80	
Thickness (mm):	
6.10	

Dimensional Tolerance (mm):

±0.2	
Optical Properties	
≥3.0	Optical Density OD (Average):
400.00	Center Wavelength CWL (nm):
±2	Center Wavelength CWL Tolerance (nm):
10.00	Full Width-Half Max FWHM (nm):
25	Minimum Transmission (%):
80-50	Surface Quality:
200 - 1200	Blocking Wavelength Range (nm):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Selectively Transmitting a Narrow Range of Wavelengths
 - Quantities Extremely Limited, Buy While Supplies Last
 - For Even More Deals, Check out [Mega Clearance: Optics](#)
- Bandpass interference filters are used extensively in a variety of biotech, biomedical, or quantitative chemical applications to selectively transmit a narrow range of wavelengths while blocking all others. Experimental Grade Bandpass Interference Filters are available in a variety of bandpass ranges in 11.8mm and 24.15mm diameter unmounted options.
- Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

