

TECHSPEC® 40mm Dia., 0.66 Numerical Aperture Uncoated, Aspheric Lens



Stock **#66-313** 3-5 DAYS

[Other Coating Options](#)

- 1 + **S\$630.75**

ADD TO CART

Qty 1-5
S\$630.75
Qty 6+
S\$504.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.1

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 20.60
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 36
Edge Thickness ET (mm): 2.56
Center Thickness CT (mm): 15.50 ±0.1
f#: 0.75
Bevel: Protective bevel as needed
Radius R₂ (mm): 400
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Power (diopters): 33.33

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View