

[See all 215 Products in Family](#)

TECHSPEC® 40mm Dia., 0.66 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-436** **13 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **\$768⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$768.60 each
Qty 6-10	\$691.60 each
Qty 11-25	\$630.00 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

40.00 +0.00/-0.025 **Diameter (mm):**

Centering (arcmin):

36.00 Clear Aperture CA (mm):

8.83 Edge Thickness ET (mm):

20.00 ±0.10 Center Thickness CT (mm):

Protective as needed Bevel:

Plano Shape of Back Surface:

Optical Properties

30.00 @ 587.6nm Effective Focal Length EFL (mm):

0.66 Numerical Aperture NA:

18.04 Back Focal Length BFL (mm):

N-SF5 Substrate: □

587.6 Aspheric Design Wavelength (nm):

0.4λ Asphere Figure Error, RMS @ 632.8nm:

Uncoated Coating:

40-20 Surface Quality:

0.75 f#:

32.25 Abbe Number (v_d):

1.673 Index of Refraction (n_d):

380 - 2500 Wavelength Range (nm):

Infinite Conjugate Distance:

587.6 Focal Length Specification Wavelength (nm):

33.33 Power (diopters):

Material Properties

7.9 Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 233:

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts