

40mm Dia. x 200mm FL, NIR II Coated, DCX N-K5 Lens



Stock #67-671 CLEARANCE 5 In Stock

[Other Coating Options](#)

1 S\$31⁸⁵

ADD TO CART

Volume Pricing	
Qty 1+	S\$31.85 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Double-Convex Lens Type:

Physical & Mechanical Properties

40.00 +0.00/-0.10 Diameter (mm):

<1	Centering (arcmin):
8.00 ±0.10	Center Thickness CT (mm):
6.07	Edge Thickness ET (mm):
39	Clear Aperture CA (mm):
Protective as needed	Bevel:
Optical Properties	
200.00 @ 587.6nm	Effective Focal Length EFL (mm):
197.36	Back Focal Length BFL (mm):
NIR II (750-1550nm)	Coating:
R _{abs} ≤ 1.5% @ 750 - 800nm R _{abs} ≤ 1.0% @ 800 - 1550nm R _{avg} ≤ 0.7% @ 750 - 1550nm	Coating Specification:
N-K5	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1.00	Focal Length Tolerance (%):
5.00	f#:
0.10	Numerical Aperture NA:
750 - 1550	Wavelength Range (nm):
8 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>


Regulatory Compliance	
Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- N-K5 Substrate
- Various Anti-Reflection (AR) Coatings
- PCX and DCX Options Available

N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

TECHNICAL INFORMATION



COMPATIBLE MOUNTS
