

[See all 13 Products in Family](#)

40X Objective, CFI Plan Achromatic

See More by [Nikon](#)



Stock #75-356 **NEW** 1 In Stock

⊖ 1 ⊕ **\$840⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	\$840.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
MRL00402

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Type:
Microscope Objective

Style:
Infinity Corrected

Manufacturer:
Nikon

Physical & Mechanical Properties

0.55 **Field of View (mm):**

59.33 **Length excluding Threads (mm):**

27 **Maximum Diameter (mm):**

120 **Weight (g):**

Optical Properties

0.17 **Compatible Cover Glass Thickness (mm):**

0.025 **Horizontal Field of View, 1/2" Sensor:**

0.22 **Horizontal Field of View, 2/3" Sensor:**

40X **Magnification:**

0.65 **Numerical Aperture NA:**

0.56 **Working Distance (mm):**

22 **Field Number (mm):**

59.89 **Parfocal Length (mm):**

N/A **Immersion Liquid:**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

M25 x 0.75 **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1X to 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1X up to 100X magnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.

Technical Information

