

TECHSPEC®

40mm Diameter x 3.3mm Thickness, Uncoated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#29-391** **8 In Stock**

-

1

+

S\$47^{.95}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$47.95 each
Qty 6-25	S\$37.80 each
Qty 26-99	S\$36.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Type of Window:

Glass

Physical & Mechanical Properties

Clear Aperture CA (mm):

36.00	
	Diameter (mm):
40.00 ±0.50	
	Thickness (mm):
3.30 ±0.2	
	Bevel:
Protective as needed	
	Clear Aperture (%):
≥90	
	Edges:
Ground and Seamed	
	Poisson's Ratio:
0.20	
	Young's Modulus (GPa):
64	
	Knoop Hardness (kg/mm²):
480.00	

Optical Properties	
	Coating:
Uncoated	
	Substrate: ☐
BOROFLOAT®	
	Index of Refraction (n _d):
1.472	
	Surface Quality:
80-50	
	Transmission (%):
90	
	Abbe Number (v _d):
65.41	
	Wavelength Range (nm):
350 - 2000	
	Surface Flatness (P-V):
4 - 6λ	

Material Properties	
	Density (g/cm³):
2.23	
	Transformation Temperature (°C):
525	
	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
3.25 (+20 to +300°C)	

Environmental & Durability Factors	
	Operating Temperature (°C):
1 hour @ 500; >100 hours @ 450	
	Resistance to Temperature Difference (K):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	
	Thermal Shock (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	


Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	

Product Details

- Low Coefficient of Thermal Expansion
 - Visible to Near Infrared Transmission
 - High Resistance to Thermal Shock
- TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts