

TECHSPEC® 4.25" Diameter x 25.5" FL Enhanced Aluminum, Parabolic Mirror



Stock #32-066-533

CONTACT US

-

1

+

S\$704.70

ADD TO CART

Qty 1-9

S\$704.70

Qty 10+

S\$598.85

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate:

BOROFLAT®

Focal Length Tolerance (%):
±1

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 25.5
Effective Focal Length EFL (mm): 647.70
Radius of Curvature (mm): 1,295.40
Aperture (f/#): f/6
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant