


LightPath 356785 | 2.75mm Dia., 0.62 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-679 CLEARANCE CONTACT US

-

1

+

S\$63.73

ADD TO CART

Qty 1+

S\$63.73

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):  
2.75 ±0.015

Effective Focal Length EFL (mm):  
1.42 @488nm

Numerical Aperture NA:  
0.62

Substrate: 

[L-LAL12](#)

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Aspheric Design Wavelength (nm):</b><br>488                        |
| <b>Coating:</b><br>BBAR (350-600nm)                                   |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <1.0% @ 350 - 600nm |
| <b>Surface Quality:</b><br>20-10                                      |
| <b>Clear Aperture CA (mm):</b><br>1.70                                |
| <b>Edge Thickness ET (mm):</b><br>0.6                                 |
| <b>Center Thickness CT (mm):</b><br>1.08 ±0.05                        |
| <b>f/#:</b><br>0.81                                                   |
| <b>Bevel:</b><br>Protective bevel as needed                           |
| <b>Lightpath Lens Code:</b><br>356785                                 |
| <b>Type:</b><br>Aspheric Lens                                         |
| <b>Wavelength Range (nm):</b><br>350 - 600                            |
| <b>Working Distance (mm):</b><br>0.86                                 |
| <b>Conjugate Distance:</b><br>Infinite                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |