

[See all 52 Products in Family](#)

TECHSPEC® 4mm f/8.0 Sealed UCw Series Fixed Focal Length Lens



UCw Series Fixed Focal Length Lenses

Stock **#70-585** **2 In Stock**

⊖ 1 ⊕ **\$394⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	\$394.80 each
Need More?	Request Quote

Product Downloads

General

UCw Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens with Compact Form Factor **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed **Iris Option:**

40.71 Length (mm):

40 Maximum Diameter (mm):

40 Outer Diameter (mm):

6.01 Maximum Rear Protrusion (mm):

40.6 Maximum Length (mm):

Optical Properties

84.8° Horizontal Field of View @ Max Sensor Format:

84.8° Horizontal Field of View, 1/2" Sensor:

77.8° Horizontal Field of View, 1/2.5" Sensor:

65.4° Horizontal Field of View, 1/3" Sensor:

49.7° Horizontal Field of View, 1/4" Sensor:

8.00 Maximum Image Circle (mm):

0.02 Numerical Aperture NA, Object Side:

8 (7) Number of Elements (Groups):

4.00 Focal Length FL (mm):

0 - ∞ Working Distance (mm):

f/8.0 Aperture (f/#):

M4 MgF₂ Coating:

M4 MgF₂ Coating Specification:

12.69 Entrance Pupil Position (mm):

16.04 Object Space Principal Plane (mm):

5.84 Image Space Principal Plane (mm):

-20.43 Maximum Distortion (%):

-12.68 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

Sensor

1/2.5" Optimized Sensor Format:

1/2" Maximum Sensor Format:

1.85 Pixel Size (µm):

Threading & Mounting

M62 x 0.75 (Male) Filter Thread:

#33-308 (Required) Filter Thread Adapter:

M40 x 0.5 (Male) Front Thread:

C-Mount Mount:

Environmental & Durability Factors

IPX7 Environmental Rating:

-20 to +60 For questions regarding operating temperature please contact our support team Storage Temperature (°C):

Waterproof (IPX7) **Type of Ruggedization:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.
