

[See all 72 Products in Family](#)

**TECHSPEC® 50 x 50mm Linear Polarizing Film (XP42-18)**



Stock #29-480 [CONTACT US](#)

- 1 + **\$37<sup>45</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>\$37.45</b> each
Qty 11-25	<b>\$29.68</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

Polarization axis is parallel to marking on protective film. **Note:**

**Physical & Mechanical Properties**

50.0 x 50.0 +0.0/-0.5 **Dimensions (mm):**

**Thickness (mm):**

0.19 ±0.03

**Construction:**

Polarizing Film

**Optical Properties**

**Coating:**

Uncoated, Protective Film on Both Sides

**Extinction Ratio:**

9000:1 (nominal at 555nm)

**Substrate:** □

**Polymer Film XP42-18**

**Transmission (%):**

Single: 42 ±2  
Parallel: 36.4  
Crossed: <0.004 (nominal at 555nm)

**Wavelength Range (nm):**

400 - 700

**Polarization Efficiency (%):**

>99.98 (nominal at 555nm)

**Transmission, Single (%):**

42 ±2

**Transmission, Parallel (%):**

36.4

**Transmission, Crossed (%):**

<0.004 (nominal at 555nm)

**Environmental & Durability Factors**

**Operating Temperature (°C):**

-40 to +80

**Heat Resistance (°C x Hours):**

80 x 500

**Cold Resistance (°C x Hours):**

60 x 90% RH x 500

**Humidity Resistance (°C x Hours):**

-40 x 500

**Regulatory Compliance**

**RoHS 2015:**

**Compliant**

**Certificate of Conformance:**

**View**

**Reach 247:**

**Compliant**

**Product Details**

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- **High-Temperature** Options Also Available

Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

**Immediate Custom Quotes Available**

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

**Technical Information**



