

TECHSPEC®

500 x 500mm High Transmission Linear Polarizing Film (XP44-40)



High Transmission Linear Polarizing Film (XP44-40)

Stock #14-352

CLEARANCE

3-5 DAYS

-

1

+

S\$385.63

ADD TO CART

Qty 1-10

S\$385.63

Qty 11+

S\$347.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Extinction Ratio:

2000:1

Substrate:

[Polymer Film XP44-40](#)

Operating Temperature (°C):

-40 to +80

Dimensions (mm):

500.0 x500.0 +0.0/-3.0
Thickness (mm): 0.40 ±0.05
Transmission (%): Single: 44.2 ±1.5 Parallel: 38.6 Crossed: <0.02
Type: Linear Polarizer
Construction: Polarizing Film
Note: The polarisation axis is parallel to the notch on the polariser
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.95

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)