

TECHSPEC®

500mm x 1000mm Linear Polarizer Film (XP42HE-18S) with Adhesive



Stock #71-907 9 In Stock

-

1

+

S\$777^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$777.00 each
Qty 11-25	S\$621.32 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Note:

Polarization axis can be identified as follows:
Circular Parts - Parallel to direction of notch on polarizer
Square Parts - Parallel to mark on protective film
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

Dimensions (mm):

500 x 1000 +/-5.0	
0.22 +/- 0.02	Thickness (mm):
Construction:	
Polarizing Film with Adhesive Backing	
Optical Properties	
30,000:1 (Nominal at 555nm)	Extinction Ratio:
Polymer Film XP42HE-18	Substrate:
Transmission (%):	
Single: 42.6 (nominal @ 555nm), 41.1 (average 420-700nm) Parallel: 36.4 (nominal @ 555nm), 34.0 (average 420-700nm) Crossed: 0.001 (nominal @ 555nm), 0.002 (average 420-700nm)	
420 - 700	Wavelength Range (nm):
Polarization Efficiency (%):	
>99.99% (nominal at 555nm)	
Environmental & Durability Factors	
-40 to +80	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Superior 30,000:1 Extinction Ratio
- Excellent Transmission from 420-700nm
- Available in a Range of Sizes
- Custom Sizes Available

TECHSPEC® Ultra-High Contrast Polarizing Film (XP42HE) are designed to produce a 30,000:1 contrast ratio from 420 – 700nm with an excellent transmission of 42.6%. These polarizing films are available in rectangular geometries in a range of sizes. TECHSPEC Ultra-High Contrast Polarizing Film (XP42HE) are easily cut to required geometries using common cutting tools for system integration. Additionally, the 500 x 1000mm version [#24-286](#) and [#71-907](#) are available with an adhesive backing to facilitate incorporation into various applications. These polarizing films are ideal for imaging, metrology, and microscopy applications where contrast sensitivity is paramount.