

[See all 46 Products in Family](#)

50.8mm Dia, 340 - 560nm, $\lambda/2$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-029** [CONTACT US](#)

⊖ 1 ⊕ **SS\$4,893.⁰⁰**

ADD TO CART

Volume Pricing

Qty 1-5	SS\$4,893.00 each
Qty 6+	SS\$4,235.00 each
Need More?	Request Quote

Product Downloads

General

Achromatic Waveplate **Type:**

Air Spaced **Configuration:**

Physical & Mechanical Properties

>34.0 **Clear Aperture CA (mm):**

Diameter (mm):

50.80

6.00 ±0.2

Thickness (mm):

+0/-0.25

Dimensional Tolerance (mm):

Crystalline

Construction:

<10

Parallelism (arcsec):

+0/-0.25

Housing Tolerance (mm):

Optical Properties

R_{avg} <0.75% @ 340 - 560nm

Coating:

Crystal Quartz and MgF₂

Substrate: □

λ/2

Retardance:

40-20

Surface Quality:

<λ/4 @ 632nm

Transmitted Wavefront, P-V:

λ/100 @ 20°C

Retardance Tolerance:

R_{avg} <0.75% @ 340 - 560nm

Coating Specification:

340 - 560

Wavelength Range (nm):

>5 J/cm² @ 1064nm, 10ns, 10Hz

Damage Threshold, By Design: □

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 247:



Product Details

- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- λ/4 and λ/2 Retardance
- Mounted in Black Anodized Aluminum Housing

Achromatic Waveplates (Retarders) provide a constant phase shift independent of the wavelength of light that is used. This wavelength independence is achieved by using two different birefringent crystalline materials. The relative shifts in retardation over the wavelength range are balanced between the two materials used. Achromatic Waveplates (Retarders), with their flat response, are ideal for use with tunable lasers, multiple laser line systems, and other broad-spectrum sources.

Designed to be used at an angle of incidence of 0°, changes of ±3° will yield less than 1% change in retardance. The 23mm clear aperture waveplates will feature a cemented construction. All Achromatic Waveplates (Retarders) are mounted in an anodized aluminum housing with the fast axis clearly indicated.

Technical Information



25.4mm Diameter Waveplates



Half Wave: 1200-1650nm



Half Wave: 700-1000nm



Half Wave: 465-610nm



Quarter Wave: 465-610nm



30.0mm Diameter Waveplates

