

TECHSPEC[®]

50.8mm Dia. Protected Aluminum Coated, Mounted Fused Silica Corner Cube Retroreflector



Mounted Fused Silica Corner Cube Retroreflectors

Stock **#15-822** **2 In Stock**

-

1

+

S\$966⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$966.00 each
Qty 6-25	S\$777.00 each
Qty 26-49	S\$721.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Retroreflector

Physical & Mechanical Properties

Diameter Tolerance (mm):

+0.0/-0.1

50.8	Inner Diameter (mm):
63.5	Outer Diameter (mm):
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25	

Optical Properties	
±3	Beam Deviation (arcsec):
Aluminum with protective overcoat	Coating:
Fused Silica (Corning 7980)	Substrate: □
20-10	Surface Quality:
Left-Handed	Image Orientation:
Coating Specification: Reflective Surfaces: R _{avg} >85% FROM400-700nm, @ 45° AOI	
180	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
0.20	Power (fringes) @ 632.8nm:
0.20	Irregularity (fringes) @ 632.8nm:

Threading & Mounting	
(2) ¼-20 Tapped Holes	Mounting Threads:


Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- ¼-20 Tapped Holes for Easy Mounting
- Excellent Transmission in the UV
- Useful for Surveying and Alignment
- Also Available [Unmounted](#)


TECHSPEC® Mounted Fused Silica Corner Cube Retroreflectors are pre-mounted in anodized aluminum housings with two ¼-20 tapped holes for easy integration into optical systems. Corner cube retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the orientation of the prism, back onto itself. Mirrors will only do this at a normal angle of incidence, making corner cube retroreflectors better suited for applications where precision alignment is difficult or time-consuming. TECHSPEC Mounted Fused Silica Corner Cube Retroreflectors are ideal for prototyping or research applications that require convenient, durable mounting solutions. These mounted retroreflectors provide excellent transmission in the UV.

Technical Information



Stock No.	Inner Diameter ID	Outer Diameter OD	H	X
#15-817	12.7	31.75	11.73	18.08
#15-818	12.7	31.75	11.73	18.08
#15-819	25.4	38.10	20.62	26.98
#15-820	25.4	38.10	20.62	26.98

#15-821	50.8	63.50	39.95	46.30
#15-822	50.8	63.50	39.95	46.30



Units: mm