

[See all 51 Products in Family](#)

TECHSPEC® 50.8mm Dia. x 75mm FL, 3-12µm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#11-431** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **SS\$2,149.⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	SS\$2,149.00 each
Qty 11-25	SS\$1,932.00 each
Qty 26-49	SS\$1,519.00 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

50.80 +0.00/-0.10 **Diameter (mm):**

≤12.7	Centering, ETD (μm):
5.50 ±0.10	Center Thickness CT (mm):
2.39	Edge Thickness ET (mm):
45.72	Clear Aperture CA (mm):
Protective as needed	Bevel:
<50 RMS	Surface Roughness (□):

Optical Properties

75.00 @ 10.6μm	Effective Focal Length EFL (mm):
72.71	Back Focal Length BFL (mm):
BBAR (3000-12000nm)	Coating:
R _{avg} ≤3.0% @ 3 - 12μm	Coating Specification:
Coherent® Infrared ZnSe	Substrate: □
40-20	Surface Quality:
λ	Power (P-V) @ 632.8nm:
λ/20	Irregularity (P-V) @ 10.6μm:
105.20	Radius R₁ (mm):
1.48	f/#:
0.34	Numerical Aperture NA:
3000 - 12000	Wavelength Range (nm):
<0.0005 @ 10.6μm	Bulk Absorption Coefficient (cm⁻¹):

Electrical

λ/10	Power (P-V) @ 10.6μm:
------	------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Edmund Optics® Designed, Coherent® Manufactured
- Premier Grade ZnSe Material
- Uncoated or Broadband AR Coating Options

TECHSPEC® Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are designed for focusing or collimation applications in the mid-wave and longwave infrared spectrum. Manufactured by Coherent®, these lenses feature Infrared ZnSe material with <0.0005cm⁻¹ bulk absorption at 10.6μm and are available uncoated or with a variety of broadband anti-reflection coating options. The 8-12μm coating is ideal for use with CO₂ lasers and thermal camera applications, whereas the dual band 3-12μm coating is ideal for hyperspectral applications. TECHSPEC® Zinc Selenide PCX Lenses feature an irregularity of <λ/20 at 10.6μm, 40-20 surface quality, and <50Å surface roughness. Three diameter options are available, with effective focal lengths ranging from 12.7mm to 250mm.

Notes: II-VI Incorporated is now Coherent Corp.

Technical Information



AR COATED ZINC SELENIDE



Typical transmission of a ZnSe window with BBAR (3000-12000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} < 5.0\% \text{ @ } 3 - 12\mu\text{m}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a ZnSe window with BBAR (8000-12000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 0.5\% \text{ @ } 8 - 12\mu\text{m}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts
