

50.8mm Length, M4 and M6, Steel Post



Stock **#72-763** NEW **20+ In Stock**

-

1

+

S\$8^{.75}

ADD TO CART

Volume Pricing	
Qty 1+	S\$8.75 each
Need More?	Request Quote

Product Downloads

General

	Type:
Metric	

Physical & Mechanical Properties

±0.1	Length Tolerance (mm):
2	Length (inches):
50.80	Length (mm):
	Diameter (inches):

0.5	
	Diameter (mm):
12.70	
	Diameter Tolerance (mm):
-0.02/-0.05	
Threading & Mounting	
	Male Thread:
Thread 1: M4 x0.7 Thread 2: M6 x 1	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	

Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x0.7/M6 x 1.0 for Metric; 8-32¹/₄-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

Note: All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.