

[See all 20 Products in Family](#)

50° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



UV Fused Silica Holographic Diffusers

Stock **#48-512** **4 In Stock**

⊖ 1 ⊕ **S\$698⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$698.60 each
Need More?	Request Quote

Product Downloads

General

Holographic Diffuser **Type:**

Physical & Mechanical Properties

21.6 ±0.1 **Clear Aperture CA (mm):**

25.00 ±0.1 **Diameter (mm):**

Mounted **Construction:**

Optical Properties

±5 **Angle Tolerance (°):**

50 (FWHM) **Diffusing Angle (°):**

Fused Silica (Corning 7980) **Substrate:** □

Typical: 90 **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

Threading & Mounting

5.00 +0.00/-0.35 **Mount Thickness (mm):**

Environmental & Durability Factors

-40 to +170 **Operating Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Product Details

- Diffusing Angles Ranging from 0.5 - 50°
- Fused Silica Substrate Ideal for High Temperatures
- Homogenous Light Distribution
- **Standard Holographic Diffusers** Also Available

UV Fused Silica Holographic Diffusers are used to control the diffuse area of illumination and increase transmission efficiency to greater than 90% from filament lamps, LEDs, arc lamps, and other sources. These UV Fused Silica Holographic Diffusers use a fused silica substrate enabling their use at higher operating temperature than **polycarbonate holographic diffusers** and offer controlled, homogenous light distribution. It is important to note that diffusing angles are given for a collimated input beam and angular divergence will vary for different incidence angles.

Unlike many holographic elements, these specific fused silica components transmit light in the UV, visible, and near-infrared. Zero order, or a specular component, of transmitted light is less than 1% for visible wavelengths. Diffusers with wider diffusing angles (10 degree FWHM or wider) can also be used in an extended range of 200-1500nm, but those with lower diffusing angles are only recommended for use between 400-700nm.

Note: Matte surface should face the light source. To clean holographic diffusers, dampen a lint free cloth wipe with methanol and gently wipe the entire diffuser surface in a gentle, circular pattern. Immediately and carefully blow off the clean diffuser area with dry compressed air. Caution: cleaning may cause a change in the optical performance of the diffuser.

Technical Information



Compatible Mounts

