

TECHSPEC® 50mm C VIS-NIR Series Fixed Focal Length Lens



50mm VIS-NIR, #67-717

Stock **#67-717** ☒ In Stock



1



S\$486.00

ADD TO CART

Qty 1+

S\$486.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:

Variable

Length (mm):

53.70

Horizontal Field of View, 1/2" Sensor:

31.0mm - 7.3°

Horizontal Field of View, 2/3" Sensor:

42.7mm - 10.0°

Filter Thread:

M30.5 x0.50 (Female)

Maximum Diameter (mm): 35.8
Outer Diameter (mm): 35.8
Weight (g): 107
Horizontal Field of View, 1/3" Sensor: 23.3mm - 5.5°
Maximum Rear Protrusion (mm): 2.85
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0436
Horizontal Field of View @ Max Sensor Format: 42.8mm - 10.0°
Number of Elements (Groups): 6 (4)
Horizontal Field of View, 1/1.8" Sensor: 34.9mm - 8.2°
Horizontal Field of View, 1/2.5" Sensor: 28.1mm - 6.6°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 50.00
Primary Magnification PMAG: 0.207
Maximum Sensor Format: 2/3"
Working Distance (mm): 250 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/22
Coating: 425 - 1000nm BBAR
Coating Specification: 425 - 1000nm BBAR
Entrance Pupil Position (mm): 33.76
Horizontal Field of View, 1/4" Sensor: 17.4mm - 4.1°
Object Space Principal Plane (mm): 39.77
Image Space Principal Plane (mm): -36.21
Field of View at Max Sensor Format: Horizontal: 42.7mm - 10° Vertical: 32mm - 7.5° Diagonal: 53.5mm - 12.5°
Maximum Distortion (%): 0.25
Exit Pupil Position (mm): -43.04
Lens Wavelength Range: VIS-NIR
Imaging Lens Type: Compact Lens Coated for Visible to Near Infared
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View