

TECHSPEC<sup>®</sup> 50mm Dia., 3mm Thick, MgF<sub>2</sub> Coated λ/4 N-BK7 Window



Stock **#37-015** [CONTACT US](#)

-

1

+

S\$187<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | <b>S\$187.60</b> each         |
| Qty 6-25       | <b>S\$149.80</b> each         |
| Qty 26-49      | <b>S\$140.00</b> each         |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

|        |           |
|--------|-----------|
| 330.00 | #Sorting: |
|--------|-----------|

General

|                   |       |
|-------------------|-------|
| Protective Window | Type: |
|-------------------|-------|

Physical & Mechanical Properties

|       |                         |
|-------|-------------------------|
| 45.00 | Clear Aperture CA (mm): |
|-------|-------------------------|

|                      |                          |
|----------------------|--------------------------|
| 50.00 +0.0/-0.25     | Diameter (mm):           |
| 3.00 ±0.20           | Thickness (mm):          |
| <1                   | Parallelism (arcmin):    |
| Protective as needed | Bevel:                   |
| 90                   | Clear Aperture (%):      |
| Fine Ground          | Edges:                   |
| 0.21                 | Poisson's Ratio:         |
| 82                   | Young's Modulus (GPa):   |
| 610.00               | Knoop Hardness (kg/mm²): |

Optical Properties

|                                       |                                        |
|---------------------------------------|----------------------------------------|
| MgF <sub>2</sub> (400-700nm)          | Coating:                               |
| N-BK7                                 | Substrate: □                           |
| 1.516                                 | Index of Refraction (n <sub>d</sub> ): |
| 60-40                                 | Surface Quality:                       |
| 64.17                                 | Abbe Number (v <sub>d</sub> ):         |
| R <sub>avg</sub> ≤1.75% @ 400 - 700nm | Coating Specification:                 |
| 400 - 700                             | Wavelength Range (nm):                 |
| λ/4                                   | Surface Flatness (P-V):                |
| 10 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, Reference:           |

Material Properties

|                                           |                                                              |
|-------------------------------------------|--------------------------------------------------------------|
| 2.51                                      | Density (g/cm³):                                             |
| 7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

Product Details


- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

TECHSPEC® λ/4 N-BK7 Precision Windows are ideally suited for industrial and low-power laser applications. The high tolerance design yields minimal beam distortion and scatter. Broadband coating options extend the range of these precision windows through the visible and near-infrared spectra. TECHSPEC® λ/4 N-BK7 Precision Windows are offered in circular and rectangular sizes ranging from 2mm to 200mm.

**Note:** New additions to this product family may be specified with a transmitted wavefront distortion (TWD) specification instead of a surface flatness. For more information on the difference between these two specifications, see our application note on [Understanding Optical Windows](#).


Technical Information





Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700nm$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880nm$   
 $R_{avg} \leq 1.25\% @ 400 - 870nm$   
 $R_{avg} \leq 1.25\% @ 890 - 1000nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.4\% @ 425 - 675nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



