

TECHSPEC[®] 50mm Dia. 400 - 750nm Broadband λ /10 ZERODUR[®] Mirror



Stock **#24-031** [CONTACT US](#)

-

1

+

S\$526⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$526.40 each
Qty 6-25	S\$421.40 each
Qty 26-49	S\$396.20 each
Need More?	Request Quote

Product Downloads

General

Type:
Flat Mirror

Physical & Mechanical Properties

Diameter (mm):
50.00 +0.00/-0.20

Commercial Polish	Back Surface:
Protective as needed	Bevel:
90	Clear Aperture (%):
Ground	Edges:
30	Parallelism (arcsec):
5.00 ±0.20	Thickness (mm):

Optical Properties	
λ 10	Surface Flatness (P-V):
ZERODUR®	Substrate: □
20-10	Surface Quality:
R _{avg} >98% @400 - 750nm (0 - 45°) R _{avg} >99% @400 - 750nm (0°)	Coating Specification:
Dielectric Mirror (400-750nm)	Coating:
Dielectric	Coating Type:
0-45	Angle of Incidence (°):
400 - 750	Wavelength Range (nm):
0.5 J/cm² @ 532nm, 20ns, 20Hz	Damage Threshold, By Design: □

Material Properties	
0.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- Enhanced Reflectivity and LDT over Metallic Coatings
- UV, Visible, and NIR Reflective Coatings Designed for 0-45° AOI
- [Metallic Coated ZERODUR®](#) Mirrors Also Available

TECHSPEC® Broadband Dielectric ZERODUR® λ 10 Mirrors combine high reflectivity over broad wavelength ranges with a near zero coefficient of thermal expansion (CTE) making them ideal for laser applications where temperature fluctuations could impact optical performance. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$, which is an order of magnitude lower than most glass types, including fused silica. Featuring coatings designed for 0-45° AOI and >99% average reflectivity, these dielectric coated mirrors provide higher reflectivity than metal coated mirrors, increasing system throughput by minimizing energy loss. TECHSPEC® Broadband Dielectric ZERODUR® λ 10 Mirrors are ideal for beam steering and beam folding applications from the UV to NIR, including [fluorescence microscopy](#), flow cytometry, and [laser communications](#).

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts