

[See all 22 Products in Family](#)

## 50mm Dia. x 100mm FL Protected Aluminum, Concave Mirror



Stock **#43-471** **20+ In Stock**

S\$88<sup>.20</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-49       | <b>S\$88.20</b> each          |
| Qty 50-99      | <b>S\$75.60</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

Spherical Mirror **Type:**

#### Physical & Mechanical Properties

$\pm 0.5$  **Thickness Tolerance (mm):**

50.00  $\pm 0.50$  **Diameter (mm):**

90 **Clear Aperture (%):**

Edge Thickness ET (mm):

6.0

## Optical Properties

Metal **Coating Type:**

Protected Aluminum (400-2000nm) **Coating:**

400 - 2000 **Wavelength Range (nm):**

100.00 **Effective Focal Length EFL (mm):**

**N-BK7** **Substrate:** □

f/2 **Aperture (f/#):**

**Coating Specification:**  
R<sub>avg</sub> >85% @400 - 700nm  
R<sub>avg</sub> >90% @400 - 2000nm

±2 **Focal Length Tolerance (%):**

200.00 **Radius R<sub>1</sub> (mm):**

80-50 **Surface Quality:**

200.00 **Radius of Curvature (mm):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

## Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

## Technical Information

