

TECHSPEC® 50mm Dia x 25mm FL 3-12μm Coated, Ge Aspheric Lens



Stock **#89-615** 3-5 DAYS
[Other Coating Options](#)

- 1 + **S\$2,737.60**

ADD TO CART

Qty 1-5
S\$2,737.60
Qty 6+
S\$2,190.08
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 50.00 +0.0/-0.1
Effective Focal Length EFL (mm): 25.00 @ 4000nm
Numerical Aperture NA: 1.00
Back Focal Length BFL (mm):

20.64
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: $\lambda/6$
Coating: BBAR (3000-12000nm)
Coating Specification: R_{avg} <5.0% @ 3 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 45
Edge Thickness ET (mm): 2.5
Center Thickness CT (mm): 7.75 ±0.10
f/#: 0.5
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 49.34
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant