

TECHSPEC[®] 50mm Dia x -100mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-663** 2 In Stock

-

1

+

S\$100⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$100.80 each
Qty 6-25	S\$81.20 each
Qty 26-49	S\$78.40 each
Need More?	Request Quote

Product Downloads

General	
Spherical Mirror	Type:
Physical & Mechanical Properties	
50.00	Diameter (mm):
5.00	Center Thickness CT (mm):

90.00	Clear Aperture (%):
+0.0/-0.1	Dimensional Tolerance (mm):
3.43	Edge Thickness ET (mm):
200.0	Radius R (mm):
±0.1	Thickness Tolerance (mm):

Optical Properties

-100.00	Focal Length FL (mm):
Protected Aluminum (400-700nm)	Coating:
R _{avg} >85% @400 - 700nm	Coating Specification:
Metal	Coating Type:
±2	Focal Length Tolerance (%):
N-BK7	Substrate: ☐
λ/2	Surface Accuracy:
60-40	Surface Quality:
400 - 700	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Precision Polished Surface
- λ/2 Surface Accuracy
- Variety of Coating Options Offered

TECHSPEC® Convex Mirrors are ideal for expanding an imaging system's field of view without introducing chromatic aberrations. TECHSPEC Convex Mirrors utilize a precision polished surface with a λ/2 surface accuracy to maintain image quality. These optical mirrors create virtual, upright images. Shorter focal lengths generate wider fields of view, while longer focal lengths minimize distortion.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).