

[See all 65 Products in Family](#)

**TECHSPEC® 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens**



50mm Focal Length



Stock #15-668 **1 In Stock**

⊖ 1 ⊕ **S\$414<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | S\$414.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Cw Series **Product Family:**

C-Mount compatible with O-ring 25mm ID x 2mm **Note:**

Fixed Focal Length Lens **Type:**

**Physical & Mechanical Properties**

|       |                               |
|-------|-------------------------------|
| Fixed | Iris Option:                  |
| 51.80 | Length (mm):                  |
| 41.00 | Maximum Diameter (mm):        |
| 41    | Outer Diameter (mm):          |
| 2.1   | Maximum Rear Protrusion (mm): |

## Optical Properties

|   |  |
|---|--|
| Horizontal: 10.0°<br>Vertical: 7.54°<br>Diagonal: 12.5° | Field of View at Max Sensor Format:      |
| 10.0°   | Horizontal Field of View, 2/3" Sensor:   |
| 8.22°   | Horizontal Field of View, 1/1.8" Sensor: |
| 7.31°   | Horizontal Field of View, 1/2" Sensor:   |
| 6.58°   | Horizontal Field of View, 1/2.5" Sensor: |
| 5.49°   | Horizontal Field of View, 1/3" Sensor:   |
| 11.00   | Maximum Image Circle (mm):               |
| 0.005   | Numerical Aperture NA, Object Side:      |
| 6 (5)   | Number of Elements (Groups):             |
| 50.00   | Focal Length FL (mm):                    |
| 100 - ∞   | Working Distance (mm):                   |
| f/16  | Aperture (f/#):                          |
| 425 - 675nm BBAR  | Coating Specification:                   |
| 41.82   | Entrance Pupil Position (mm):            |
| -11.85  | Object Space Principal Plane (mm):       |
| -38.15  | Image Space Principal Plane (mm):        |
| 0.257   | Maximum Distortion (%):                  |
| -40.88  | Exit Pupil Position (mm):                |
| VIS   | Lens Wavelength Range:                   |

## Sensor

|      |                        |
|------|------------------------|
| 2/3" | Maximum Sensor Format: |
| 2.74 | Pixel Size (µm):       |

## Threading & Mounting

|                    |                |
|--------------------|----------------|
| M36 x0.50 (Female) | Filter Thread: |
| C-Mount            | Mount:         |

## Environmental & Durability Factors

|                             |                           |
|-----------------------------|---------------------------|
| IPX7 and IPX9K              | Environmental Rating:     |
| -20 to +60                  | Storage Temperature (°C): |
| Waterproof (IPX7 and IPX9K) | Type of Ruggedization:    |

## Regulatory Compliance

## Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


## Technical Information




#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Distortion Plot



#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f16



#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f16



#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f16



#15-668, 50mm, f/16 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f16