

TECHSPEC® 514.5nm, 25mm Diameter, Raman Edge Filter



Stock **#86-241** [CONTACT US](#)

⊖ 1 ⊕ **\$S\$1,029.50**

ADD TO CART

Qty 1-9
\$S\$1,029.50
Qty 10+
\$S\$855.50
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm):

519.60
Design Wavelength DWL (nm): 514.5
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 416 - 514.5
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <5.1
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >600
Coating Specification: T _{avg} ≥93% @ 521.2 - 1160.5nm
Wavelength Range (nm): 416 - 1161
Laser Blocking Wavelength (nm): 514.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View